

COOKWARE (PTFE)




DURIT Dynamic

This product is a light ceramic-reinforced non-stick coating for everyday use. The product is also attractive due to its good price-performance ratio.

- Durable water-based product
- Good non-stick effect
- Effective scratch and abrasion resistance
- Three-layer system with good price-performance ratio
- Also available as a version without Maximizing green

Properties

Number of layers	3
Coating thickness	30 - 35 µm / 1.18 - 1.38 mils
Curing temperature to approx	420 °C / 788 °F
Service temperature	250 °C / 482 °F
Scratch resistance	★ ★ ★ ★ ★
Abrasion (BS)	★ ★ ★ ★ ★
Non-stick effect (LGA)	★ ★ ★ ★ ★
Non-stick effect (LGA and milk)	★ ★ ★ ★ ★
Corrosion resistance (EU 10/2011)	★ ★ ★ ★ ★



DURIT Dynamic is a universal, three-layer, water-based non-stick system. Due to its generally good performance such as non-stick effect, abrasion resistance and corrosion resistance, the product is particularly suitable for everyday use.

1. Resistant surface sealing for long durability
2. Slightly reinforced ceramic middle layer for good wear resistance
3. Primer with excellent adhesion to the substrate
4. Specially prepared substrate for an optimum adhesion of the coating to the cookware product

Substrate

Substrate	Pre-treatment	Suitability
pressed / forged alu	alkaline degrease	✓ ✓ ✓
alu cast	sandblasting with corundum	✓ ✓ ✓
stainless steel	sandblasting with corundum	✓ ✓ ✓

COOKWARE (PTFE)



Cleaning and care instructions

After use, clean the pan with hot water, a mild washing-up liquid and a sponge cloth or the fine side of a dishwashing sponge. A soft dishwashing brush can also be used for cleaning. Always wipe the pan dry before storing it.

Stubborn leftovers should never be cleaned with a metal sponge or the sharp side of a dishwashing sponge. Instead, soak the product in warm soapy water and then carefully clean the surface. Poorly cleaned items significantly reduce the non-stick effect and destroy the coating.

The product can be cleaned in the dishwasher, although this is not recommended due to the aggressive cleaning agents. Cleaning by hand is preferable.

Instructions for use

Before using the product for the first time, remove the packaging, labels and all stickers and clean the pan with hot water and washing-up liquid.

Never heat cookware unattended or empty on the hob. A drop of oil as a temperature indicator is helpful to recognize overheating. As such, the use of a bit cooking oil or fat enhances the flavor of the food.

The use of plastic or wooden utensils is recommended to avoid damaging the surface seal.

Longevity

Higher temperatures during heating can lead to discoloration and therefore destroy the non-stick coating.

All coatings are sensitive to scratches and cuts. Small scratches are visible, but do not impair the properties. Nevertheless, we do not recommend the use of metal cutlery and other sharp objects in cookware. Instead, the use of plastic or wooden utensils is recommended.

A small amount of grease or a drop of oil will also significantly extend the life of the product.

Temperature stability

As a general rule, never heat an empty pan. Especially not on induction hobs. Critical temperatures can be reached quickly.

PTFE pans can be heated up to 230 °C (446 °F) in continuous use and up to 250 °C (482 °F) for short periods. This is the reason why PTFE pans are only suitable for searing to a limited extent.

Overheating can lead to discoloration and the reduction of the non-stick effect. Overheating can also cause bubble formation or separating of the coating.

DURIT Dynamic